

# SECULIFE | HIT<sub>AM</sub> and SECULIFE | HIT<sub>MD</sub> TRMS Medical-Multimeter

3-349-453-03  
7/5.16

## Digital TRMS handheld multimeter with 23 functions

- Voltage measurement
- Auto-ranging current measurement from 100  $\mu$ A (resolution: 10 nA) to 10 A (16 A)
- Capacitance and resistance measurement, diode and continuity testing
- Measuring categories: 600 V CAT III and 300 V CAT IV
- 1 kHz low-pass filter
- TRMS AC and AC+DC, 20 kHz bandwidth
- Data memory for more than 15,000 measured values
- Extremely rugged, dust and water-proof variant with IP65
- **SECULIFE HIT<sub>AM</sub>: Housing, protective rubber holster and set of measuring cables each with antimicrobial properties**
- **SECULIFE HIT<sub>MD</sub>: Multimeter with hygiene expertise**

## Interface

- Bidirectional infrared interface for communication with the PC
- IR-USB adapter available as option

## Power Supply

- Battery operation
- Mains operation via optional broad range variable power pack

IP65

3  
YEARS  
WARRANTY

MADE IN  
GERMANY



German  
Accreditation Body  
D-K-15080-01-01  
DAKKS Calibration Certificate as Standard Feature



## Applications

The multimeter has been designed especially for use in the field of medical technology, amongst other purposes for servicing, repairing and testing medical devices.

## Features

### SECULIFE HIT<sub>AM</sub>

The multimeters of the **SECULIFE HIT<sub>AM</sub>** series have been endowed with antimicrobial properties. This is to curb the growth of germs, counteract microbial colonization or kill microorganisms.

### SECULIFE HIT<sub>MD</sub>

**SECULIFE HIT<sub>MD</sub>** is protected against the penetration of fluids and resistant to disinfectants. A hygiene expertise has been issued by the Department for Medical Microbiology and Hygiene at the Philipps University Marburg to confirm the suitability for use in hygienically sensitive areas.

On the basis of the specifications set forth by the Deutsche Gesellschaft für Hygiene und Mikrobiologie (DGHM) (*German Association for Hygiene and Microbiology*) and the Vereinigung für Angewandte Hygiene (VAH) (*Association for Applied Hygiene*) the possibilities for safe disinfection of the **SECULIFE HIT<sub>MD</sub>** have been tested. The tests were performed with regard to test microbes in analogy and in conformity with the specifications for disinfection methods set forth by the Deutsche Gesellschaft für Hygiene und Mikrobiologie (DGHM) within the framework of a stress test in a practice-related context.

### Three Connector Jacks with Automatic Blocking Sockets (ABS) \*

All current ranges are implemented via a single connector jack which prevents any possibility of operator error. Beyond this, the automatic blocking sockets prevent incorrect connection of the measurement cables, as well as selection of the wrong measured quantity. Danger to the user, the instrument and the device under test resulting from operator error is thus ruled out.

\* Patented (patent no. EP 1801 598 and US 7,439,725)

### Overload Protection

The instrument is safeguarded for up to 1000 V in all measuring functions by overload protection. Voltages of greater than 1000 V and current of greater than 10 or 16 A are indicated acoustically. Dangerous contact voltages are indicated when the 1 kHz low-pass filter is activated.

The FUSE display appears in order to indicate that the fuse for the current measuring input has blown.

### RMS Value with Distorted Waveshape

The utilized measuring method allows for waveshape independent RMS measurement (TRMS AC and AC+DC) for voltage and current up to 20 kHz.

### Activatable Filter for V AC Measurement

A 1 kHz low-pass filter can be activated if required, for example when measuring at electronic frequency converters or switched-mode power supplies.

### High Voltage sensor

The input signal is examined for contact danger regardless of the selected input function or filtering.

# SECULIFE | HITAM and SECULIFE | HITMD

## TRMS Medical-Multimeter

### Measuring 5 V Square-Wave Signals

This function makes it possible to test circuits and transmission cables by measuring the frequency and the keying ratio of pulses with amplitudes of 2 to 5 V and frequencies of 100 Hz to 1 MHz.

### Analog Scale for Quick Trend Display – Bar Graph or Pointer

The analog scale (with additional negative range for zero-frequency quantities) allows for faster recognition of measured value fluctuation than is possible with a digital display.

The instrument can be switched back and forth between bar graph and pointer display.

### Automatic or Manual Measuring Range Selection

Measured quantities are selected by means of a rotary switch and a function key. The measuring range is automatically matched to the measured values. The measuring range can also be selected and fixed manually with a key.

### Fast Acoustic Continuity Test

Testing for short circuiting and interruption is possible with the selector switch in the  $\square$ ) position. The threshold value for acoustic signaling can be set to 1, 10, 20, 30, 40 or 90  $\Omega$ .

### Automatic Storage of Measured Values \*

The DATA function automatically saves the digitally displayed measured value after settling in. Acoustic signaling is also used to indicate whether the new measured value deviates from the initial reference value by less or more than 0.1% of the measuring range.

\* Patented

### Storage of Min-Max Values

Comparable to the slave-pointer function of an analog instrument, the device saves the highest and lowest measured values after the MIN/MAX function has been activated or reset. These extreme values can be queried at the display. The values are acquired using an especially fast sampling rate (40 measurements per second).

### Battery Charging Status – Power Saving Circuit

The battery charge level is indicated by means of a 4-segment symbol.

The device is switched off automatically if the measured value remains unchanged for a period of between 10 and 59 minutes (adjustable), and if none of the controls are activated during this time. Automatic shutdown can be deactivated by switching the instrument to continuous operation.

### Protective Cover for Harsh Conditions

The instrument is protected against damage in the event of impacts or dropping by means of a soft rubber cover with tilt stand and test probe holder. The rubber material also assures that the instrument does not wander if it is set up on a vibrating surface.

### Infrared Data Interface

The device can be remote configured, and momentary and stored measurement data can be read out via the bidirectional infrared interface. The USB X-TRA interface adapter and METRAWIN 10 software are required to this end (see accessories). Interface protocol and device driver software for LabVIEW® (National Instruments™) are available upon request. The infrared interface can be switched off in the standby mode.

### DAkkS Calibration Certificate

The multimeters are furnished with an internationally valid DAkkS calibration certificate (recognized by EA and ILAC). After the specified calibration interval has elapsed (recommended interval: 1 to 3 years), the multimeters can be inexpensively recalibrated in our own DAkkS calibration laboratory.

### Functions

Voltage $V_{AC}$ TRMS ( $R_i \geq 9 M\Omega$ )	100 mV / 1 V / 10 V / 100 V / 1000 V
Frequency Hz @ $V_{AC}$	100 Hz / 1 kHz / 10 kHz / 100 kHz
Voltage Lo $^{1)}$ $V_{AC}$ TRMS ( $R_i = 1 M\Omega$ )	100 mV / 1 V / 10 V / 100 V / 1000 V
Frequency Hz @ Lo $^{1)}$ $V_{AC}$	100 Hz / 1 kHz / 10 kHz / 100 kHz
Low-pass filter	$\overline{1kHz}$ @ Lo $V_{AC}$ or @ Hz
Voltage $V_{DC}$ ( $R_i \geq 9 M\Omega$ )	100 mV / 1 V / 10 V / 100 V / 1000 V
Voltage $V_{AC+DC}$ TRMS ( $R_i \geq 9 M\Omega$ )	100 mV / 1 V / 10 V / 100 V / 1000 V
Bandwidth @ $V_{AC+DC}$ or $V_{AC}$	20 kHz
Frequency MHz @ 5 V AC $\square$	100 Hz...1 MHz
Duty cycle %	2,0 % ... 98 %
Resistance $\Omega$	100 $\Omega$ / 1 k $\Omega$ / 10 k $\Omega$ / 100 k $\Omega$ / 1 M $\Omega$ / 10 M $\Omega$ / 40 M $\Omega$
Continuity test $\square$ )	0 ... 100 $\Omega$ @ $I_{CONST} = 1$ mA
Diode measurement	0 ... 5,1 V @ $I_{CONST} = 1$ mA
Temperature measurement °C / °F @ $T_C$	Thermocouple Type K
Temperature measurement °C / °F @ $R_{TD}$	Pt100 / Pt1000
Capacitance measurement F	10 nF / 100 nF / 1 $\mu$ F / 10 $\mu$ F / 100 $\mu$ F / 1000 $\mu$ F
Current $A_{DC}$	100 $\mu$ A / 1 mA / 10 mA / 100 mA / 1 A / 10 A (16 A)
Current $A_{AC+DC}$ TRMS	100 $\mu$ A / 1 mA / 10 mA / 100 mA / 1 A / 10 A (16 A)
Current $A_{AC}$ TRMS	100 $\mu$ A / 1 mA / 10 mA / 100 mA / 1 A / 10 A (16 A)
Bandwidth @ $A_{AC+DC}$ or $A_{AC}$	10 kHz
Frequency Hz @ $A_{AC}$	100 Hz / 1 kHz / 10 kHz / 30 kHz
Data logger function $^{2)}$ (memory)	4 Mbit = 500 kByte = 15400 measured values
IR-Interface	38400 Bd
Power pack connector socket	✓
Protection	IP65
Measurement category	600 V CAT III and 300 V CAT IV
DAkkS calibration certificate	✓
Protective rubber cover	✓

1) Alternating voltage measurement with specially reduced input impedance

2) Sampling rate adjustable from 0.1 seconds to 9 hours

### Applicable Regulations and Standards

IEC/DIN EN 61010-1 VDE 0411-1	Safety requirements for electrical equipment for measurement, control and laboratory use
DIN EN 61326-1 VDE 0843-20-1	Electrical equipment for measurement, control and laboratory use – EMC requirements – Part 1: General requirements
DIN EN 60529 DIN VDE 0470-1	Test instruments and test procedures – degrees of protection provided by enclosures (IP code)

### Voluntary Manufacturer's Guarantee

24 months for materials and workmanship  
1 to 3 years for calibration (depending upon application)

# SECULIFE | HITAM and SECULIFE | HITMD TRMS Medical-Multimeter

## Characteristic Values

Meas.-Function	Measuring Range	Resolution at Upper Range Limit		Input Impedance		Intrinsic Uncertainty under Reference Conditions			Overload Capacity <sup>2)</sup>	
		11999	1199	≡	~ / ≚	±(... %rdg. + ... d)	±(... %rdg. + ... d)	±(... %rdg. + ... d)	Value	Time
<b>V</b>	100 mV	10 μV		≥ 9 MΩ	≥ 9 MΩ // < 50 pF	0.09 + 5 mit ZERO	1 + 30 (> 300 d) <sup>1)</sup>	1 + 30 (> 300 d) <sup>1)</sup>	1000 V DC AC RMS sine <sup>6)</sup>	continuous
	1 V	100 μV		≥ 9 MΩ	≥ 9 MΩ // < 50 pF	0.05 + 3	0.5 + 9 (> 200 d)	1 + 30 (> 300 d)		
	10 V	1 mV		≥ 9 MΩ	≥ 9 MΩ // < 50 pF	0.05 + 3	0.5 + 9 (> 200 d)	1 + 30 (> 300 d)		
	100 V	10 mV		≥ 9 MΩ	≥ 9 MΩ // < 50 pF	0.05 + 3	0.5 + 9 (> 200 d)	1 + 30 (> 300 d)		
	1000 V	100 mV		≥ 9 MΩ	≥ 9 MΩ // < 50 pF	0.09 + 3	0.5 + 9 (> 200 d)	1 + 30 (> 300 d)		
				Voltage drop, approx. at upper range limit		≡	~ <sup>10)</sup>	≚ <sup>10)</sup>		
<b>A</b>	100 μA	10 nA		12 mV	12 mV	0.5 + 5	1.5 + 10 (> 200 d)	1.5 + 30 (> 200 d)	0.2 A	continuous
	1 mA	100 nA		120 mV	120 mV	0.5 + 3	1.5 + 10 (> 200 d)	1.5 + 30 (> 200 d)		
	10 mA	1 μA		16 mV	16 mV	0.5 + 3	1.5 + 10 (> 200 d)	1.5 + 30 (> 200 d)		
	100 mA	10 μA		160 mV	160 mV	0.5 + 3	1.5 + 10 (> 200 d)	1.5 + 30 (> 200 d)		
	1 A	100 μA		40 mV	40 mV	0.9 + 10	1.5 + 10 (> 200 d)	1.5 + 30 (> 200 d)		
	10 A	1 mA		600 mV	600 mV	0.9 + 10	1.5 + 10 (> 200 d)	1.5 + 30 (> 200 d)		
				Open-circuit voltage Meas. curr. @ range limit		±(... %rdg. + ... d)				
<b>Ω</b>	100 Ω	10 mΩ		< 1.4 V	Approx. 300 μA	0.2 + 5 with active ZERO function			1000 V DC AC RMS sine	Max. 10 s
	1 kΩ	100 mΩ		< 1.4 V	Approx. 250 μA	0.2 + 5				
	10 kΩ	1 Ω		< 1.4 V	Approx. 100 μA	0.2 + 5				
	100 kΩ	10 Ω		< 1.4 V	Approx. 12 μA	0.2 + 5				
	1 MΩ	100 Ω		< 1.4 V	Approx. 1.2 μA	0.2 + 5				
	10 MΩ	1 kΩ		< 1.4 V	Approx. 125 nA	0.5 + 10				
	40 MΩ	10 kΩ		< 1.4 V	Approx. 20 nA	2.0 + 10				
<sup>4)</sup> 100 Ω	—	0.1 Ω	Approx. 8 V	Approx. 1 mA const.	3 + 5					
<b>→</b> 5.1 V <sup>3)</sup>	—	1 mV	Approx. 8 V	Approx. 1 mA const.	0.5 + 3					
				Discharge resist. U <sub>0 max</sub>		±(... %rdg. + ... d)				
<b>F</b>	10 nF	10 pF		10 MΩ	0.7 V	1 + 6 <sup>4)</sup> with active ZERO function			1000 V DC AC RMS sine	Max. 10 s
	100 nF	100 pF		1 MΩ	0.7 V	1 + 6 <sup>4)</sup>				
	1 μF	1 nF		100 kΩ	0.7 V	1 + 6 <sup>4)</sup>				
	10 μF	10 nF		12 kΩ	0.7 V	1 + 6 <sup>4)</sup>				
	100 μF	100 nF		3 kΩ	0.7 V	5 + 6 <sup>4)</sup>				
	1000 μF	1 μF		3 kΩ	0.7 V	5 + 6 <sup>4)</sup>				
				f <sub>min</sub> <sup>5)</sup>		±(... %rdg. + ... d)				
<b>Hz (V)</b> <b>Hz (A)</b>	100.00 Hz	0.01 Hz				0.05 + 3 <sup>8)</sup>			Hz (V) <sup>6)</sup> : 1000 V	Max. 10 s
	1.0000 kHz	0.1 Hz			1 Hz					
	10.000 kHz	1 Hz			10 Hz					
<b>Hz (V)</b> <b>Hz (A)</b>	100.00 kHz	10 Hz			10 Hz				Hz (A): <sup>7)</sup>	
	30.00 kHz	10 Hz			10 Hz					
<b>MHz</b>	100 Hz ... 1 MHz	0.01 ... 100 Hz			1 ... 100 Hz	0.05 + 3	> 2 V ... 5 V			
<b>%</b>	2.0 ... 98 %	—	0.01 %	100 Hz ... 1 kHz	1 Hz	0.1 R	> 2 V ... 5 V		1000 V	Max. 10 s
	5.0 ... 95 %	—	0.01 %	... 10 kHz	1 Hz	0.1 R per kHz	> 2 V ... 5 V			
	10 ... 90 %	—	0.01 %	... 100 kHz	1 Hz	0.1 R per kHz	> 2 V ... 5 V			
						±(... %rdg. + ... d)				
<b>°C/°F</b>	Pt100	-200.0 ... +850.0 °C				0.3 + 15 <sup>9)</sup>			1000 V DC/AC RMS sine	Max. 10 s
	Pt1000	-150.0 ... +850.0 °C	0.1 °C			0.3 + 15 <sup>9)</sup>				
	K (NiCr-Ni)	-250.0 ... +1372.0 °C				1% + 5 K <sup>9)</sup>				

<sup>1)</sup> Values of less than 200 digits are suppressed in the mV range.  
15 (20) ... 45 ... 65 Hz ... 20 (1) kHz sinusoidal. See influence error on page 4.

<sup>2)</sup> At 0° ... + 40° C

<sup>3)</sup> Displays up to max. 5.1 V, "OL" in excess of 5.1 V.

<sup>4)</sup> Applies to measurements at film capacitors

<sup>5)</sup> Lowest measurable frequency for sinusoidal measuring signals symmetrical to the zero point

<sup>6)</sup> Overload capacity of the voltage measurement input:  
power limiting: frequency x voltage max. 3 x 10<sup>9</sup> V x Hz for U > 100 V

<sup>7)</sup> Overload capacity of the current measurement input:

See current measuring ranges for maximum current values.

<sup>8)</sup> Input sensitivity, sinusoidal signal, 10% to 100% of the measuring range

<sup>9)</sup> Plus sensor deviation

<sup>10)</sup> Residual value deviates within 1 ... 30 d from the zero point due to TRMS converter when probe tips are short-circuited

<sup>11)</sup> Off-time > 30 min and T<sub>A</sub> ≤ 40 °C

Key: R = measuring range, d= digit(s), rdg. = measured value (reading)

### Internal Clock

Time format DD.MM.YYYY hh:mm:ss

Resolution 0.1 s

Accuracy ±1 min. per month

Temperature Influence 50 ppm/K

# SECULIFE | HITAM and SECULIFE | HITMD

## TRMS Medical-Multimeter

### Influencing Quantities and Influence Error

Influencing Quantity	Sphere of Influence	Measured Quantity / Measuring Range <sup>1)</sup>	Influence Error (...% rdg. + ... d) / 10 K
Temperature	-10° C ... +21° C and +25° C ... +50° C	V $\equiv$	0.2 + 10
		V $\sim$	0.4 + 10
		100 $\Omega$ ... 1 M $\Omega$	0.5 + 10
		> 1 M $\Omega$	1 + 10
		mA/A $\equiv$	0.5 + 10
		mA/A $\approx$	0.8 + 10
		10 nF ... 100 $\mu$ F	1 + 5
		Hz	0.2 + 10
		°C/°F (Pt100/Pt1000)	0.5 + 10
°C/°F thermocouple K	0.2 + 10		

<sup>1)</sup> With zero balancing

Influencing Qty.	Meas. Qty. / Meas. Range	Sphere of Influence	Intrinsic Uncertainty <sup>3)</sup> $\pm$ ( ... % rdg. + ... d)	
Frequency	V <sub>AC</sub>	100.00 mV	> 15 Hz ... 45 Hz	3 + 30
			> 65 Hz ... 1 kHz	2 + 30
			> 1 kHz ... 10 kHz	3 + 30
		1.0000 V ... 100.00 V	> 15 Hz ... 45 Hz	2 + 9
			> 65 Hz ... 1 kHz	1 + 9
			> 1 kHz ... 20 kHz	3 + 9
	1000.0 V <sup>2)</sup>	> 15 Hz ... 45 Hz	2 + 9	
		> 65 Hz ... 1 kHz	2 + 9	
		> 1 kHz ... 10 kHz	3 + 30	
		A <sub>AC</sub>	100.00 $\mu$ A ... 10.0000 A	> 15 Hz ... 45 Hz
> 65 Hz ... 10 kHz	> 65 Hz ... 10 kHz			

<sup>2)</sup> Power limiting: frequency x voltage max.  $3 \times 10^6$  V x Hz for U > 100 V

<sup>3)</sup> The accuracy specification for frequency response is valid within a display value range of 10% to 100% of the measuring range for both measuring modes with the TRMS converter in the AC and (AC+DC) ranges.

Influencing Quantity	Sphere of Influence	Measured Quantity / Measuring Range	Influence Error <sup>5)</sup>
Crest factor CF	1 ... 3	V $\sim$ , A $\sim$	$\pm$ 1 % rdg.
	> 3 ... 5		$\pm$ 3 % rdg.

<sup>5)</sup> Except for sinusoidal waveshape

Influencing Quantity	Sphere of Influence	Measured Quantity	Influence Error
Relative humidity	75%	V, A, $\Omega$ , F, Hz, °C	1 x intrinsic uncertainty
	3 days instrument off		
Battery voltage	1.8 to 3.6 V	ditto	Included in intrinsic uncertainty

Influencing Quantity	Sphere of Influence	Measured Quantity / Measuring Range	Damping
Common Mode Interference Voltage	Interference quantity max. 1000 V $\sim$	V $\equiv$	> 120 dB
		1 V $\sim$ , 10 V $\sim$	> 80 dB
		100 V $\sim$	> 70 dB
		1000 V $\sim$	> 60 dB
Series Mode Interference Voltage	Interference quantity: V $\sim$ , respective nominal value of the measuring range, max. 1000 V $\sim$ , 50 Hz ... 60 Hz, sine	V $\equiv$	> 50 dB
		V $\sim$	> 110 dB

### Reference Conditions

Ambient temperature	+23 °C $\pm$ 2 K
Relative humidity	40 ... 75%
Measured qty. frequency	45 ... 65 Hz
Measured qty. waveshape	Sine
Battery voltage	3 V $\pm$ 0.1 V

### Response Time (after manual range selection)

Measured Quantity / Measuring Range	Response Time Digital Display	Measured Quantity waveshape
V $\equiv$ , V $\sim$ AV $\equiv$ , A $\sim$	1.5 s	From 0 to 80% of upper range limit value
100 $\Omega$ ... 1 M $\Omega$	2 s	
10/40 M $\Omega$	5 s	
Continuity	< 50 ms	From $\infty$ to 50% of upper range limit value
°C (Pt 100)	Max. 3 s	
$\rightarrow$	1.5 s	From 0 to 50% of upper range limit value
10 nF ... 100 $\mu$ F	Max. 2 s	
1 000 $\mu$ F	Max. 7 s	
> 10 Hz	1.5 s	

### Data Interface


Type	Optical via infrared light through the housing
Data transmission	Serial, bidirectional (not IrDa compatible)
Protocol	Device specific
Baud rate	38,400 baud
Functions	<ul style="list-style-type: none"> <li>Select/query measuring functions and parameters</li> <li>Query momentary measurement data</li> <li>Read out stored measurement data</li> </ul>

The USB X-TRA plug-in interface adapter (see accessories) is used for adaptation to the PC's USB port.

### Internal Measured Value Storage

Memory capacity	4 MBit / 540 kB for approx. 15,400 measured values with date and time stamp
-----------------	---

### Power Supply

Battery	2 ea. 1.5 V mignon cell (2 ea. size AA), alkaline manganese per IEC LR6 (2 ea. 1.2 V NiMH rechargeable battery also possible)
Service life	with alkaline manganese: approx. 200 hours
Battery test	Battery capacity display with battery symbol in 4 segments:  . Querying of momentary battery voltage via menu function.
Power OFF function	Multimeter is switched off automatically: <ul style="list-style-type: none"> <li>If battery voltage drops to below prox. 1.8 V</li> <li>If none of the keys or the rotary switch are activated for an adjustable duration of 10 to 59 minutes, and the multimeter is not in the continuous operation mode</li> </ul>

# SECULIFE | HITAM and SECULIFE | HITMD

## TRMS Medical-Multimeter

**Power pack socket** If the NA X-TRA power pack has been plugged into the instrument, the batteries are disconnected automatically. Rechargeable batteries can only be recharged externally.

### Display

LCD panel (65 mm x 36 mm) with analog and digital display including unit of measure, type of current and various special functions

### Background illumination

Background illumination is switched off approximately 1 minute after it has been activated.

### Analog

**Display** LCD scale with bar graph or pointer, depending on the selected parameter setting

**Scaling** With 4 division lines each, 1 bar/pointer corresponds to 500 digits at the digital display

**Polarity display** With automatic switching

**Overflow display** With the ► symbol

**Measuring rate** 40 measurements per second and display refresh

### Digital

**Display / char. height** 7-segment characters / 15 mm

**Number of places** 4½ place  $\pm$  11,999 steps

**Overflow display** "OL" is displayed for  $\geq$ 12,000 digits

**Polarity display** "-" (minus sign) is displayed if plus pole is connected to "⊥"

**Measuring rate** 10 and 40 measurements per second with the Min-Max function except for the capacitance, frequency and keying ratio measuring functions

**Refresh rate** 2 times per sec., every 500 ms

### Acoustic Signals

**For voltage** Intermittent signal at above 1000 V

**For current** Intermittent signal at above 10 A  
continuous signal at above 16 A

### Fuse

**Fuse** FF (UR) 10 A/1000 V AC/DC;  
10 mm x 38 mm,  
Switching capacity: 30 kA at 1000 V AC/DC, protects the current measurement input in the 100  $\mu$ A through 10 A ranges

### Electrical Safety

Per IEC 61010-1:2010/DIN EN 61010-1:2011/VDE 0411-1:2011

Safety class	II	
Measuring category	III	IV
Operating voltage	600 V	300 V
Fouling factor	2	
Test voltage	6.7 kV~	

### Electromagnetic Compatibility (EMC)

**Interference emission** EN 610326-1: 2006, class B

**Interference immunity** EN 610326-1: 2006  
EN 610326-2-1: 2006

### Ambient Conditions

**Accuracy range** 0 °C ... +40 °C

**Operating temp. range** -10° C ... +50 °C

**Storage temp. range** -25° C ... +70 °C (without batteries)

**Relative humidity** Max.75%, no condensation allowed

**Elevation** To 2000 m

**Deployment** Indoors, except within specified ambient conditions

### Mechanical Design

**Housing** Impact resistant plastic (ABS)

**Dimensions** 200 x 87 x 45 mm  
(without protective rubber cover)

**Weight** Approx. 0.35 kg with batteries

**Protection** Housing: IP 65

Table excerpt regarding significance of the IP code

IP XY (1 <sup>st</sup> digit X)	Protection against penetration of solid particles	IP XY (2 <sup>nd</sup> digit Y)	Protection against penetration by water
6	Dust-proof	5	Jet-water

### Included

- multimeter  
**SECULIFE HITAM:** 1 pair of safety measurement cables antimicrobial (1.5 m) with 4 mm test probes, 600 V CAT III, 300 V CAT IV (KS17-2AMB)  
**SECULIFE HITMD:** 1 pair of safety measurement cables (1.5 m) with 4 mm test probes, 600 V CAT III, 300 V CAT IV (KS17-2)
- batteries, 1.5 V, type AA
- condensed operating instructions, English/German
- Detailed operating instructions for download from our website at [www.seculife.eu](http://www.seculife.eu)
- DAkkS calibration certificate
- protective rubber cover
- HC20 hard case

# SECULIFE | HITAM and SECULIFE | HITMD TRMS Medical-Multimeter

## Accessories for Operation at a PC

### Interface Adapter for USB Connection

The USB X-TRA bidirectional interface adapter includes the following functions:

- Configure the **SECULIFE HITAM** from a PC.
- Transmit live measurement data to the PC.
- Read out data from memory at the **SECULIFE HITAM**.

The adapter does not require a separate power supply. Its baud rate is 38,400 baud. A CD ROM is included which contains current drivers for Windows operating systems.



## METRAwin<sup>®</sup>10/METRAHit<sup>®</sup> Software

METRAwin<sup>®</sup>10/METRAHit<sup>®</sup> PC software is a multilingual, measurement data logging program for recording, visualizing and documenting measured values from **SECULIFE HITAM** multimeters. Communication between the PC and the measuring instrument(s) is established via available interfaces and memory adapters. Telephone modems can be interconnected as well.

Depending upon device type, one or several of the following operating modes are possible:


- **Device Configuration**  
Remote configuration and querying of device-specific functions and parameters, for example measuring function, measuring range and memory parameters. Frequently used device settings can be saved to configuration files for easy recall.
- **Online Recording of Measurement Data**  
Read-in, display and recording of momentarily measured data from the interconnected device.
  - Number of measuring channels up to 10
  - Start recording manual, triggered by measured value, time triggered
  - Recording mode
    - > time controlled with sampling interval of 0.05 s\* ... 1 s ... 60 min
    - > manually controlled
    - > measured value controlled in event of exceeded limit/delta value
  - Recording duration max. 10 million intervals

\* Depending upon device type, measuring function, number of measuring channels and communication (e.g. via modem), sample intervals of less than 1 s cannot be used.


- **Reading Out and Visualizing Stored Data**  
If supported by the device: read-in and display of offline data recorded to device memory.

For purposes of analysis, data recorded online or read in from the device's memory can be displayed in various formats:

### Y(t)-recorder display for up to 6 channels




### XY-recorder display for up to 4 channels



### Multimeter-display for up to 4 channels



### Tabular display for up to 10 channels



## System Requirements

METRAwin 10 (as from version 6.0) can be run on IBM compatible PCs with Microsoft Windows<sup>®</sup> VISTA, 7, 8 and 10.

# SECULIFE | HITAM and SECULIFE | HITMD TRMS Medical-Multimeter

## Order Information

Designation	Type	Article Number
4½-place (12,000 digits) TRMS multimeter with direct, alternating and pulsating voltage measurement (TRMS values), frequency measurement, resistance measurement, continuity test, diode measurement and temperature measurement with type K thermocouples, precision temperature measurement with Pt100 or Pt1000 platinum resistance thermometers, frequency and keying ratio measurement, broad range capacitance measurement, LCD with 15 mm characters, analog bar graph and background illumination Measuring categories: 300 V/CAT IV, 600 V/CAT III, with power pack socket and IR interface, 4 MB data memory		
Housing, protective rubber holster and set of measuring cables with antimicrobial properties	SECULIFE HITAM	M687A*
„Hospital“ TRMS multimeter for use in hygienic sensitive areas, resistance against desiccation/liquids	SECULIFE HITMD	M687B
<b>Accessories for operation at a PC</b>		
IR-USB bidirectional interface adapter	USB X-TRA	Z216C
METRAwin10 software	METRAwin10	GTZ3240000R0001
<b>Accessories for temp. measurement with resistance thermometer</b>		
Pt100 temperature sensor for surface and immersion measurement, -40 to +600° C	Z3409	GTZ3409000R0001
Pt1000 temperature sensor for measurement in gases and liquids, -50 to +220° C	TF220	Z102A
Pt100 oven sensor, -50 to +550° C	TF550	GTZ3408000R0001
<b>Replacement fuse</b>		
Fuses (pack of 10)	FF (UR) 10 A / 1000 V AC/DC	Z109L
Power pack	NA X-TRA	Z218G

\* Supply in preparation



## Transport Accessories

### HitBag Cordura Belt Pouch

For multimeters (with/without protective rubber cover)



### HC20 Hard Case

For multimeter (with/without protective rubber cover) and accessories



### F836 Ever-Ready Case

For multimeter and accessories



### F829 Carrying Pouch

For multimeters (with/without protective rubber cover) and accessories



Designation	Type	Article Number
Imitation leather carrying pouch	F829	GTZ3301000R0003
Cordura belt pouch	HitBag	Z115A
Soft belt pouch large for one Multimeter. Made of rugged and water repellent Cordura, three separate cases for leads, clips, manual, CD, etc.	HitBag L	Z115B
Imitation leather ever-ready case with cable compartment	F836	GTZ3302000R0001
Hard case for one Multimeter and accessories	HC20	Z113A
Hard case for two Multimeter and accessories	HC30	Z113A

For additional information regarding accessories please refer to:

- our Measuring Instruments and Testers catalog.
- our website [www.gossenmetrawatt.com](http://www.gossenmetrawatt.com)

# SECULIFE | HITAM and SECULIFE | HITMD

## TRMS Medical-Multimeter

Current Measuring Accessories								
All current sensors and transformers are equipped with a connector cable (1.2 to 1.5 m long) with 4 mm safety banana plugs								
Type	Designation	Measuring Range	Meas. Category	Max. Wire Dia.	Transformation Factor	Frequency Range	Intrinsic Uncertainty ±(% rdg. + ...)	Article Number
<b>DC/AC Current Sensors with Voltage Output</b>								
CP30	DC/AC clip-on current sensor, with battery mode (30 h)	5 mA to 30 A (DC / AC pk)	300 V / CAT III	25 mm	100 mV/A	DC...20 kHz (-3 dB)	1 % +2 mA	Z201B
CP330	DC/AC clip-on current sensor, with 2 measuring ranges, battery mode (50 h)	Range: 0.5 ... 30 A Range: 5 ... 300 A (DC / AC rms)	300 V / CAT III	25 mm	10 mV/A; 1 mV/A	DC...20 kHz (-3 dB)	1 % + 50 mA 1 % + 100 mA	Z202B
CP1100	DC/AC clip-on current sensor, with 2 measuring ranges, battery mode (50 h)	Range: 0.5 ... 100 A Range: 5 ... 1000 A (DC / AC rms)	300 V / CAT III	32 mm	10 mV/A; 1 mV/A	DC...20 kHz (-1 dB)	1 % + 100 mA 1 % + 500 mA	Z203B
CP1800	DC/AC current clamp sensor, with 2 measuring ranges, battery mode (50 h)	Range: 0.5 ... 125 A Range: 5 ... 1250 A (DC / AC rms)	300 V / CAT III	32 mm	10 mV/A, 1 mV/A	DC ... 20 kHz (-1 dB)	1% + 100 mA 1% + 500 mA	Z204A
<b>AC Current Sensors with Voltage Output</b>								
WZ12B	AC clip-on current sensor	10 mA~ ... 100 A~	300 V / CAT III	15 mm	100 mV/A	<u>45 ... 65</u> ... 500 Hz	1.5% +0.1 mA	Z219B
WZ12C	AC clip-on current sensor, with 2 measuring ranges	1 mA~ ... 15 A~, 1 ... 150 A~	300 V / CAT III	15 mm	1 mV/mA, 1 mV/A	<u>45 ... 65</u> ... 400 Hz	3% + 0.15 mA, 2% + 0.1 A	Z219C
WZ11B	AC clip-on current sensor, with 2 measuring ranges	0.5 ... 20 A~, 5 ... 200 A~	600 V / CAT III	20 mm	100 mV/A, 10 mV/A	<u>30...48 ... 65</u> ... 500 Hz	1 ... 3%	Z208B
Z3512A	AC clip-on current sensor, with 4 measuring ranges	1 mA ... 1/10/100/ 1000 A~	600 V / CAT III	52 mm	1 V/A, 100 mV/A, 10 mV/A, 1 mV/A	<u>10...48 ... 65</u> ... 3 kHz	0.5 ... 3%, 0.2 ... 1%	Z225A
METRAF-LEX3000	Flexible AC current sensor with 3 measuring ranges, battery mode (2000 h)	0,5 ... 30 A, 0,5 ... 300 A, 5 ... 3000 A	1000 V CAT III 600 V CAT IV	176 mm	100 mV/A, 10 mV/A, 1 mV/A	10 Hz ... 20 kHz	1% + 0.1 A 1% + 0.1 A 1% + 1 A	Z207E
METRAF-LEX300M	Flexible AC miniature current sensor with 3 measuring ranges, battery mode (150 h)	1 ... 3 A, 1 ... 30 A, 5 ... 300 A	1000 V CAT III 600 V CAT IV	50 mm	1 V/A, 100 mV/A, 10 mV/A	20 Hz ... 100 kHz	1% + 0.2 A 1% + 0.2 A 1% + 1 A	Z207M
<b>AC Current Transformer with Current Output</b>								
WZ12A	AC clip-on current transformer	15 ... 180 A~	300 V / CAT III	15 mm	1 mA/A	<u>45 ... 65</u> ... 400 Hz	3%	Z219A
WZ12D	AC clip-on current transformer	30 mA ... 150 A~	300 V / CAT III	15 mm	1 mA/A	<u>45 ... 65</u> ... 500 Hz	2.5% +0.1 mA	Z219D
WZ11A	AC clip-on current transformer	1 ... 200 A~	600 V / CAT III	20 mm	1 mA/A	<u>48 ... 65</u> ... 400 Hz	1 ... 3%	Z208A
Z3511	AC clip-on current transformer	4 ... 500 A~	600 V / CAT III	30 x 63 mm	1 mA/A	<u>48 ... 65</u> ... 1 kHz	3% +0.4 A	GTZ3511 000R0001
Z3512	AC clip-on current transformer	0.5 ... 1000 A~	600 V / CAT III	52 mm	1 mA/A	<u>30...48 ... 65</u> ... 5 kHz	0.5% ... 0.7%	GTZ3512 000R0001
Z3514	AC clip-on current transformer	1 ... 2000 A ~	600 V / CAT III	64 x 150 mm	1 mA/A	<u>30...48 ... 65</u> ... 5 kHz	0.5% +0.1 A	GTZ3514 000R0001
<b>Shunt Resistors for Multimeters without Current Measuring Function</b>								
NW300mA	Plug-in shunt resistor, encapsulated 1 Ω	0 ... 300 mA	300 V / CAT III	—	1 mV/mA	DC ...10 kHz	0.5%	Z205C
NW3A	Plug-in shunt resistor, encapsulated 0,1 Ω	0 ... 3 A	300 V / CAT III	—	100 mV/A	DC ...10 kHz	0.5%	Z205B

Edited in Germany • Subject to change without notice • PDF version available on the Internet

 GOSSEN METRAWATT

GMC-I Messtechnik GmbH  
Südwestpark 15  
90449 Nürnberg • Germany

Phone +49 911 8602-111  
Fax +49 911 8602-777  
E-Mail info@seculife.eu  
www.seculife.eu